Safety Rail Height – 3 Models

LOW - This is our classic SleepSafe® bed with safety rails extending 10¾" to 18½" above the mattress depending on the foundation choice.

MEDIUM - The SleepSafe® II provides protection ranging from 10½" to 28" above the mattress depending on the foundation choice.

TALL - The SleepSafer® provides protection up to 371/4" above the mattress depending on the foundation choice. The SleepSafer® Extension Kit offers an additional 16¾" of safety rail height when ordered or retrofitted to your existing SleepSafer® Bed.



salety fall fieldlit when ordered of fetrolitted to your existing sleeps	Juici Deu.	SleepSafe® SleepSafe®	II SleepSafer®
,		Medium Bed	Tall Bed
Specifications S	leepSafe®	SleepSafe® II	SleepSafer®
SAFETY RAIL HEIGHT Distance from the top of mattress to the top of the safety rail			
Fixed Foundation with Box Spring (Choice of settings) 123	¾"or 10¾"	22¼", 18¼" or 14¼"	31½", 27½" or 23½"
Fixed Foundation with Bunkie Board (Choice of settings) 183	½" or 16½"	28", 24" or 20"	37¼", 33¼" or 29¼"
Manual Articulating Foundation 163	1/2"	24" or 18"	32¾"
Manual HI-LO Foundation LO	12½" to HI 1" above rail	LO 20" to HI 8½" or LO 14" to HI 2½"	LO 28¾" to HI 17¼"
Articulating Foundation (Choice of settings) 14"	"or 11½"	19½", 16½", 13½" or 10½"	32½", 29" or 25½"
Electric HI-LO Foundation (LO to HI Settings)	13" to HI 3" above rail	LO 23" to HI 7"	LO 31¾" to HI 15¾"
MATTRESS HEIGHT Distance from the top of the mattress to the floor.			
Fixed Foundation with Box Spring (Choice of settings) 23"	" or 25"	23½", 27½", or 31½"	23¼", 27¼" or 31¼"
Fixed Foundation with Bunkie Board (Choice of settings) 17"	or 19"	17½", 21½" or 25½"	17½", 21½" or 25½"
Manual Articulating Foundation 193	1/4"	21¾" or 25¾"	22"
Manual HI-LO Foundation LO	23¼" to HI 34¾"	LO 25¾" to HI 37¼" or LO 31¾" to HI 43¼"	LO 26" to HI 371/2
Articulated Foundation (Choice of settings) 213	¾" or 24¼"	26¼", 29¼", 32¼" or 35¼"	22", 25½", or 29¼"
Electric HI-LO Foundation - (LO to HI Settings)	22¾" to HI 38¾"	LO 22¾" to HI 38¾"	LO 23" to HI 39"
FLOOR TO RAIL HEIGHT Distance from the top of the rail to the floor. 353	3/4"	45¾"	54¾"
OVERALL OUTSIDE DIMENSIONS			
Twin 423	¼"W x 80½"L x 43"H	42¼"W x 80½"L x 53"H	42¼"W x 80¼"L x 57"H
Full 56"	"W x 80"L x 43"H	56"W x 80"L x 53"H	56"W x 80"L x 57"H
Queen 65"	"W x 80"L x 43"H	65"W x 80"L x 53"H	65"W x 80"L x 57"H
MATTRESS SIZE			
Twin 37"	"W x 77"L	37"W x 77"L	37"W x 77"L
Full 51"	"W x 77"L	51"W x 77"L	51"W x 77"L
Queen 60"	"W x 77"L	60"W x 77"L	60"W x 77"L
UNDER BED FLOOR CLEARANCE			
Standard Model 7¾	i"	7¾"	7¾"
Manual Foundation Model 7"		7¾"	7¾"
TRANSFER HEIGHT Distance from the top edge of the folded down safety rail to the floor. (Subtract 2" if safety rail is removed)	V2"	32½"	261/2"







